

JungleMUX Equipment:

**Course Title:** JungleMUX – Hands-on Training Location: Customer site within Canada or USA **Course Contents and Duration: Full Course** (4 to 5 days, 7 hours/day, see Note 2) **SONET 101 Overview Product Structure**  Description, operation and configuration of common equipment as relevant to customer's system Description, operation and configuration of interface units as relevant to customer's system **Explanation of Node Assignment Drawings**  Interpretation of Alarms System Maintenance and Troubleshooting Hands-on exercises **Topic-Specific Courses:** • VistaNET NMS Software (½ day) • OC-48, OC-12 or New OC-3 Unit (1 day) • Ether-1000 or Ether-100 Unit (½ day) • CDAX Unit (½ day) CS Service Unit (½ day) The above topic-specific courses may be combined in one course. Also see Notes 1 and 2. **Prerequisites: Full Course:** Basic Electronic Theory, Fiber Optic Transmission Principles, Digital Transmission Theory, System Testing and Measurement, "SONET 101 for JungleMUX Users" Self-Paced Course (the workbook is emailed as soon as the course is scheduled) **Topic-Specific Courses:** Completion of a full 4/4.5/5-day JungleMUX course. Date: Proposed by customer. The full course usually starts on a Monday. The customer is required to fill out the JungleMUX Training Request Form available on http://www.gedigitalenergy.com/communications/Traini ng/Lentronics.asp. Language: **English** 

charge.

JungleMUX nodes are required in the classroom for all courses offered. If the customer cannot provide them, Demo Nodes can be provided by GE at no additional



**Training material:** Training manuals are provided either in hardcopy or

softcopy (PDF) format as preferred by the customer.

**Number of students:** 6 (For additional students, to a maximum of 9,

additional charges apply. See table below.)

## **Cost:**

Course	Duration	Price (US\$) for class	Fee (US\$) per each additional
Type	(days)	with $\leq 6$ students*	student (to a maximum of 9)*
Full	4-5	\$12,430	\$1,365
Topic Specific	1	\$6,490	\$340
	1.5	\$7,480	\$510
	2	\$8,470	\$680
	2.5	\$9,460	\$850
	3	\$10,450	\$1,020

<sup>\*</sup> All applicable taxes and duties are extra.

## **Equipment provided by customer:**

Description	Quantity
JungleMUX Nodes (powered up in the training	Minimum 3
room). See Note 4.	
Patchcords with LC connectors (FC connectors for	2 per node
legacy OC-1 and OC-3 units). See Note 4.	
Multimedia LCD Projector with a minimum	1 of each
resolution of 1024x728 pixels (connects to	
instructor's laptop), screen, white board (or paper	
board), set of markers, power strip, extension	
cords (as needed)	
Laptop Computer (Windows 7, COM port)	3 (see Note 3)

- **Note 1:** A minimum of 1 day of training must be ordered.
- **Note 2:** The actual duration of the course will be determined based on the number of different types of units used in your system.
- Note 3: Some USB-to-COM port adapters cannot properly work with VistaNET software! (GE recommends use of Keyspan P/N USA-19HS for reliable operation. See http://www.tripplite.com/sku/USA19HS.)
- **Note 4:** Not applicable if demo nodes are provided by GE.