



BiTRONICS M871

Single Line, Dual Bus Modular IED

Advanced measuring, recording and communications characteristics as well as utility-grade construction make the M871 ideal for applications in AC T&D systems.

A Complete Solution for Monitoring and Recording Substation Applications

Applications

The M871 provides a low-cost entry into disturbance recording through a distributed approach. The M871 can be installed locally on a per-feeder basis. It can also be interconnected via peer-to-peer GOOSE messaging that allows cross-triggering to occur without the need to hard-wire the contacts - it thus provides a scalable approach to station-level recording.

The M871 complements relays by providing independent, high fidelity waveform capture. It provides 2 waveform recorders, 2 disturbance recording modes and trend recording - not typically found even in the most advanced digital relays. It also provides features such as fault location and SCADA communications that can automate a substation when electro-mechanical relays are used.

The M871 can replace conventional measuring instruments (measurement centres), as well as trend, sequence-of-event, disturbance and station fault recorders.

The ability to simultaneously support multiple physical links and protocols allows easy integration in retrofit applications or new substation automation projects. The M871 serves as a front-end to SCADA, while providing system-wide access to important substation data.

Measurement Features

- Ultra-fast RMS voltage and current updates each 1/4 cycle
- Full measurement set including: V, I, F, P, Pf, H (63), THD, K-factor, voltage and current unbalance, impedance and sequence components
- Available 0.2% revenue-class energy measurement (requires S11 or S12 signal input module)
- Highly accurate measurement (voltage and current better than 0.1% of reading)
- 6 AC voltage, 4 AC current and 2 auxiliary AC/DC measurement inputs
- Exceptional dynamic range - linear to 600 Vac and 100 A (requires S10 signal input module)
- Signal frequency from 15-70 Hz
- 128 samples/cycle sampling rate (256 for 7 channels)
- Accommodates 2, 2 1/2 and 3 element systems (field configurable) with field selectable CT and PT ratios

Measurement and Analysis Functions

The M871, with its multi-mode recording and high speed, high accuracy measurements, can measure and analyse:

- Network faults
- Reactions of protective devices
- Dynamic response of the network
- Long-term trends
- Revenue readings
- Substation equipment performance

Key Benefits

- Low-cost entry into substation automation monitoring and recording applications
- Monitor system stability with six simultaneous recorders and extensive non-volatile memory
- Synchronised records between multiple 70Series IEDs
- Flexible and easy interface with multiple protocols and physical links



Recording Features

- 2 waveform recorders can capture input signals at 128 samples/cycle (6.4/7.68 kHz) and up to 100 A symmetrical (S10 signal input option). Sampling rates of 32 or 64 samples/cycle, as well as 256 samples/cycle on a reduced number of channels can also be selected
- 2 separate disturbance recorders with selectable sample rates of 1-3600 cycles
- Long-term trend data of up to 230 selectable parameters
- Sequence of event recording of 5000 events, time stamped to 1 microsecond
- Automatic event notification via Ethernet or serial comms
- Extensive onboard non-volatile memory for recording
- Simultaneous recording of all recorders
- Triggering with hysteresis from any analogue threshold value, rate-of-change of analogue value, digital input, internal parameter, or “virtual” input (GOOSE messages)
- User selectable pre- and post-trigger times and three trigger modes
- GOOSE inputs stored in waveform and disturbance records

Communications Features

- 1 RS232 and 3 configurable RS232/RS485 ports supporting baud rates from 9600 to 38400. Ports can support protocols, display, or de-modulated IRIG-B signal. Modulated IRIG B adapter available
- 10BASE-T / 100BASE-T and optional 100 Mb (100BASE-FX) fibre-optic port
- Supports DNP3.0 Level 2, DNP3.0 TCP/IP, DNP3.0/UDP, Modbus RTU, Modbus TCP/IP, ZMODEM, FTP, Telnet, UCA2 (including GOOSE messaging), NTP and IEC 61850 protocols
- Optional detached display for local indication of 3-phase measured parameters

Design

The BiTRONICS M871 uses a modular design based on the CompactPCI® bus. The modular design allows the substation design engineer to specify or alter a configuration in order to meet the measurement and communications needs of a particular substation application. The rugged, aluminium housing is designed for mounting at the rear of AC switch-board panels.

There are three chassis sizes:

- Standard chassis (8.5", 216 mm wide)
- Intermediate chassis (11.65", 296 mm wide)
- Long chassis (13.45", 342 mm wide)

The standard chassis accommodates up to 2 optional modules, the inter-mediate chassis accommodates up to 4 optional modules and the long chassis accommodates up to 5 optional modules.

Standard Components

- Wide range universal power supply (20-300 Vdc/55-275 Vac)
- Signal input module linear to 100 A and 600 Vac
- Host/analog processors consisting of a 486 Processor 32-bit DSP, 16-bit A/D converter and extensive RAM and non-volatile memory

Optional Modules

- 1 A or 5 A nominal / 4 A or 20 A peak signal input module that allows the M871 to achieve 0.2% revenue accuracy (IEC 60687, ANSI C12-20-1998, EN62053-22)
- 2 different Ethernet choices: (10/100 copper, copper plus 100 Mb fibre)
- Transducer input module
- Digital I/O modules with either 8 inputs and 4 outputs or 16 inputs and 4 outputs
- P32 module allows GOOSE inputs to be recorded in waveform record

Software

A CD is provided with each M871 containing the self-installing 70 series software. The installation provides a single front-end from which all parts of the 70 series software can be launched.

The 70 series software provides Windows® based tools to manage the configuration and the analysis of the multiple data streams provided by the M871.

GEGridSolutions.com

IEC is a registered trademark of Commission Electrotechnique Internationale. IEEE is a registered trademark of the Institute of Electrical Electronics Engineers, Inc.

GE and the GE monogram are trademarks of General Electric Company.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

M871-Brochure-EN-2018-12-Grid-GA-0792. © Copyright 2018, General Electric Company. All rights reserved.

For more information please contact
GE
Grid Solutions

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact
Phone: +44 (0) 1785 250 070



Imagination at work